

Product data sheet

Characteristics

NSYBP128

Spacial SF rear panel external fixing -
1200x800 mm



Main

Range	Spacial
Accessory / separate part category	Enclosure accessory
Product or component type	Rear panel
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting location	Rear of enclosure
Quantity per set	Set of 1

Complementary

Range compatibility	Spacial Spacial SF
Device composition	Fixing elements 1 rear panel
Material	Steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Fixing mode	By screws - screw type captive - from the outside of enclosure location
Height	Nominal: 1200 mm
Width	Nominal: 800 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	77.5 cm
Package 1 Length	120.0 cm
Package 1 Weight	13.0 kg
Unit Type of Package 2	P12
Number of Units in Package 2	10
Package 2 Height	46.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	144.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Contractual warranty	
Warranty	18 months