

Product data sheet

Characteristics

NSYCEJD28

Cables passages, diameter 28-29mm. Mounted in cable entry matrix.Pkg 10



Main

Range	Spacial
Product or component type	Gasket for cable with connectors
Accessory / separate part category	Cable management accessory
Device application	Multi-purpose
Range compatibility	Spacial Spacial S3D compact enclosure Spacial Spacial CRN compact enclosure Spacial Spacial SF suitable enclosure Spacial Spacial S3CM control enclosure Spacial Spacial SBM industrial box Thalassa Thalassa PLA suitable enclosure Thalassa Thalassa PHD suitable enclosure Thalassa Thalassa PLM compact enclosure Thalassa Thalassa PLS insulating modular box
Device composition	1 gasket
Quantity per set	Set of 10

Complementary

Accessory / separate part destination	Cable
Mounting support	Cable entries plate for connectors
Material	Thermoplastic rubber
Total cable entry number	1
Cable entry number	1 x 28...29 mm
Cable outer diameter	28...29 mm
Net weight	0.019 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	4 cm
Package 1 Length	5 cm
Package 1 Weight	15 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5.5 cm
Package 2 Width	19 cm
Package 2 Length	11.5 cm
Package 2 Weight	194 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	17.5 cm
Package 3 Width	23 cm
Package 3 Length	19.5 cm
Package 3 Weight	1100 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------