

Product data sheet

Characteristics

NSYCRS10W240V

Climasys Ultra thin resistance heater low starting current 12W 240V 130x250mm



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Ultra thin resistance heater
Power range	12 W
Input voltage	240 V AC 50/60 Hz
Electrical connection	Cable length: 2 m

Complementary

Operating position	Vertical Horizontal
Ambient air temperature for operation	-60...70 °C
Temperature setting range	-40...70 °C
Material	Silicone rubber
Height	110 mm external:
Width	140 mm external:
Depth	1.6 mm external:
Device composition	6 self-adhesive Velcro pads 6 plastic spacers 4 Telequick nuts 4 clip-on nuts Fixing accessories
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By 4 screws
Mounting support	Standard mounting plate Adhesive Velcro DIN rail Telequick mounting plate

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	25.5 cm
Package 1 Length	28.5 cm
Package 1 Weight	280.0 g
Unit Type of Package 2	PAM
Number of Units in Package 2	440
Package 2 Height	172.0 cm
Package 2 Width	100.0 cm

Package 2 Length	120.0 cm
Package 2 Weight	137.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------