

Product data sheet

Characteristics

NSYDCE2410

Cable entry matrix 24/10. Systems for introduction of premanufactured cables.



Main

Range	Spacial
Product or component type	Cable entry plate for connector
Accessory / separate part category	Cable management accessory
Device application	Multi-purpose
Range compatibility	Spacial Spacial S3D compact enclosure Spacial Spacial CRN compact enclosure Spacial Spacial SF suitable enclosure Spacial Spacial S3CM control enclosure Spacial Spacial SBM industrial box Thalassa Thalassa PLA suitable enclosure Thalassa Thalassa PHD suitable enclosure Thalassa Thalassa PLM compact enclosure Thalassa Thalassa PLS insulating modular box
Device composition	1 fixing elements 1 plate
Quantity per set	Set of 1

Complementary

Accessory / separate part destination	Connector
Mounting support	Body of enclosure Cable gland plate
Material	Polyamide
Fixing mode	By fixing element
Total cable entry number	10
Cable entry number	10
Height	14 mm real:
Width	146 Mm real: 112 Mm cut-out: 130 mm fixing center:
Depth	58 Mm real: 36 Mm cut-out: 32 mm fixing centre:
Net weight	0.136 kg

Environment

IP degree of protection	IP54
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	8 cm
Package 1 Length	17 cm
Package 1 Weight	136 g
Unit Type of Package 2	CAR

Number of Units in Package 2	10
Package 2 Height	20 cm
Package 2 Width	20 cm
Package 2 Length	30 cm
Package 2 Weight	1.536 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------