

Product data sheet

Characteristics

NSYID186

Spacial SF/SM plain internal door - 1800x600 mm



Main

| | |
|------------------------------------|--|
| Range | Spacial |
| Accessory / separate part category | Enclosure accessory |
| Product or component type | Door |
| Application | Multi-purpose |
| For enclosure nominal dimensions | - |
| Mounting location | Front |
| Range compatibility | Spacial Spacial SMX Spacial Spacial SFX Spacial Spacial SF Spacial Spacial SM |
| Device composition | 1 door 2 lock with 3 mm double bar insert 1 handle Fixing elements |
| Quantity per set | Set of 1 |

Complementary

| | |
|-------------------|-----------------------------------|
| Material | Sheet steel |
| Colour | Grey (RAL 7035) |
| Surface finish | Epoxy-polyester powder |
| Lock type | Lock 3 mm double bar |
| Number of locks | 2 |
| Adjustment | Adjustable in depth every 25 mm |
| Door type | Internal plain |
| Door opening side | Reversible |
| Maximum load | 15 kg/m ² |
| Height | Nominal: 1800 mm Real: 1665 mm |
| Width | Nominal: 600 mm Real: 500 mm |
| Depth | 19.5 mm |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 7.0 cm |
| Package 1 Width | 56.0 cm |
| Package 1 Length | 173.0 cm |
| Package 1 Weight | 18.0 kg |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |

Logistical informations

| | |
|-------------------|----|
| Country of origin | ES |
|-------------------|----|

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|