

Product data sheet

Characteristics

NSYMP2016

Spacial SF/SM mounting plate - 2000x1600 mm



Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting plate description	Plain
Range compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX
Device composition	1 mounting plate 2 sliding shoes
Quantity per set	Set of 1
Material	Galvanised steel

Complementary

Fixing mode	By fixing brackets
Maximum load	300 kg/m²
Permanent permissible load	500 Kg intermediate position 600 kg back of the enclosure
Height	Fixing centers: 1850 mm Nominal: 2000 mm Real: 1897 mm
Width	Fixing centers: 1450 mm Nominal: 1600 mm Real: 1496 mm
Depth	27 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	191.0 cm
Package 1 Width	151.0 cm
Package 1 Length	4.0 cm
Package 1 Weight	75.3 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	10
Package 2 Height	152 cm
Package 2 Width	200 cm
Package 2 Length	49 cm
Package 2 Weight	745 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------