

Product data sheet

Characteristics

NSYSC1260

Spacial SF/SM canopy - 1200x600 mm



Main

Range	Spacial
Accessory / separate part category	Enclosure accessory
Product or component type	Canopy
Application	Multi-purpose
Range compatibility	Spacial Spacial SM Spacial Spacial SF
For enclosure nominal dimensions	-
Mounting location	On top of enclosure
Device composition	1 canopy Fixing elements Drilling template

Complementary

Quantity per set	Set of 1
Material	Galvanised steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Fixing mode	By screws - roof drilled holes location
Height	85 mm
Width	Nominal: 1200 mm Real: 1207 mm
Depth	625 Mm real: 600 mm nominal:

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	63.5 cm
Package 1 Length	122.0 cm
Package 1 Weight	12.185 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Logistical informations

Country of origin	ES
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------