

Product data sheet

Characteristics

NSYSC840

Spacial SF/SM canopy - 800x400 mm



Main

Range	PanelSeT
Accessory / separate part category	Enclosure accessory
Product or component type	Canopy
Application	Multi-purpose
Range compatibility	PanelSeT PanelSeT SM PanelSeT PanelSeT SF
For enclosure nominal dimensions	-
Mounting location	On top of enclosure
Device composition	1 canopy Fixing elements Drilling template




Complementary

Quantity per set	Set of 1
Material	Galvanised steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Fixing mode	By screws - roof drilled holes location
Height	85 mm
Width	800 Mm nominal: 807 mm real:
Depth	400 Mm nominal: 425 mm real:

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	44.500 cm
Package 1 Length	82.500 cm
Package 1 Weight	6.481 kg
Unit Type of Package 2	P12
Number of Units in Package 2	10
Package 2 Height	45.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	76.810 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Logistical informations

Country of origin	ES
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------