

Product data sheet

Characteristics

NSYSC850

Spacial SF/SM canopy - 800x500 mm



Main

| | |
|------------------------------------|--|
| Range | PanelSeT |
| Accessory / separate part category | Enclosure accessory |
| Product or component type | Canopy |
| Application | Multi-purpose |
| Range compatibility | PanelSeT PanelSeT SM PanelSeT PanelSeT SF |
| For enclosure nominal dimensions | - |
| Mounting location | On top of enclosure |
| Device composition | 1 canopy Fixing elements Drilling template |

Complementary

| | |
|------------------|---|
| Quantity per set | Set of 1 |
| Material | Galvanised steel |
| Colour | Grey (RAL 7035) |
| Surface finish | Epoxy-polyester powder |
| Fixing mode | By screws - roof drilled holes location |
| Height | 85 mm |
| Width | Nominal: 800 mm Real: 807 mm |
| Depth | 525 Mm real: 500 mm nominal: |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.5 cm |
| Package 1 Width | 53.5 cm |
| Package 1 Length | 82.0 cm |
| Package 1 Weight | 7.364 kg |

Offer Sustainability

| | |
|----------------------------|--|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |

Logistical informations

| | |
|-------------------|----|
| Country of origin | ES |
|-------------------|----|

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|