

Product data sheet

Characteristics

TCSMCN1FQM2

Modbus shielded cable - M12 connector - SUB-D15 - 2 m



Main

Range of product	Telemecanique Radio frequency identification XG
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part designation	Modbus shielded connecting cable
Accessory / separate part destination	Modbus/Uni-Telway network Tap-off box
Cable length	2 m

Complementary

Product compatibility	TSXSACA62 TCSAMT31FP
Electrical connection	1 male connector SUB-D 15 15 pins straight A coding 1 connector M12 straight A coding
Colour	Black
Net weight	0.27 kg



Environment

IP degree of protection	IP67
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm
Package 1 Width	16 cm
Package 1 Length	16 cm
Package 1 Weight	194 g

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------

Wiring Diagram

Modbus Connections



Pin no.		Signal
1	-	Drain (Modbus-SHLD)
2	Red	+ 24 VDC
3	Black	0 V/Modbus-GND
4	White	D0
5	Blue	D1
Connector casing		Shielding