

Product data sheet

Characteristics

VCFN25GE

TeSys Vario enclosed, emergency stop switch disconnecter, 20A, IP55



Main

Range	TeSys
Product name	TeSys Mini-VARIO
Device short name	VCFN
Product or component type	Emergency stop switch disconnecter
Performance level	Standard
Poles description	3P
Control type	Rotary handle
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 4...8 mm

Complementary

Marking	0 - 1
[Ue] rated operational voltage	690 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ithe] conventional enclosed thermal current	20 A
[Ie] rated operational current	14.5 A (AC-23A) at 400 V
Rated operational power in W	7.5 kW at 400 V (AC-23) 5.5 kW at 400 V (AC-3)
Intermittent duty class	30
Making capacity (I Rms)	250 A at 400 V AC-21A
[Icw] rated short-time withstand Rms current	150 A at 400 V duration: 1 s
Rated conditional short-circuit current	10 kA at 400 V
Suitability for isolation	Yes
Fire resistance	960 °C conforming to IEC 60595-2-1
Handle front plate dimension	60 x 60 mm
Height	131 mm
Width	82.5 mm
Depth	106 mm
Net weight	0.512 kg

Environment

Standards	IEC 60947-4-1
Protective treatment	TC
Mechanical robustness	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	11.500 cm
Package 1 Length	13.500 cm
Package 1 Weight	350.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	7
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.689 kg
Unit Type of Package 3	P06
Number of Units in Package 3	112
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	51.024 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------