

Product data sheet

Characteristics

VW3A3E307S371

Profibus DP V1 communication card, Altivar,
1.5Mbps, 9 way female SUB D connector

Main

Product or component type	Communication card
Range compatibility	Altivar 71 Plus Altivar 61 Plus
Communication port protocol	Profibus DP V1
Connector type	9-way female SUB-D connector
Transmission rate	187.5 kbps 93.75 kbps 9600 bps 12 Mbps 6 Mbps 19.2 kbps 3 Mbps 500 kbps 1.5 Mbps

Complementary

Number of addresses	1...126
Communication service	CiA 402 profile I/O profile I/O data Communication monitoring can be inhibited, adjustable PPO type 5 PPO type 3 PPO type 4 PPO type 8
Display type	1 LED for DX (data exchange) 1 LED for ST (status) Graphic display terminal for control word received Graphic display terminal for I/O data Graphic display terminal for reference received
Net weight	0.3 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	10.0 cm
Package 1 Length	20.0 cm
Package 1 Weight	500.0 g

Contractual warranty

Warranty	18 months
----------	-----------