

Product data sheet

Characteristics

VW3A3E317

CC Link communication card, Altivar, 10Mbps, removable screw connector

Main

Product or component type	Communication card
Range compatibility	Altivar 61 Plus Altivar 71 Plus
Communication port protocol	CC-Link
Connector type	Removable screw connector, 5 contacts at intervals of 3.81
Transmission rate	5 Mbps 625 kbps 156 kbps 2.5 Mbps 10 Mbps
Physical interface	2-wire RS 485

Complementary

Number of addresses	1...64
Communication service	Communication monitoring I/O data CC-Link drive profile
Display type	1 LED for L.ERR (Error) 1 LED for L.RUN (Running) 1 LED for power 1 LED for RD (Receive Data) 1 LED for SD (Send Data) Graphic display terminal for drive address Graphic display terminal for transmission speed used
Net weight	0.3 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	17.5 cm
Package 1 Length	23.5 cm
Package 1 Weight	300.0 g

Contractual warranty

Warranty	18 months
----------	-----------