

Product data sheet

Characteristics

XACF3250

empty pendant control station XAC-F - custom openings



Main

Range of product	Harmony XAC
Product or component type	Pendant control station
Device short name	XACF


Complementary

Control station type	Double insulated
Enclosure material	Glass reinforced polyester
Electrical circuit type	Control circuit
Enclosure type	Empty enclosure
Number of cut-out	30 maximum in positions requested on the order form
Control station colour	Yellow
Cable entry	Rubber sleeve with stepped entry 22...35 mm
Guard rail	Without
Standards	CSA C22.2 No 14
Protective treatment	TH
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102
Mechanical durability	1000000 cycles
Net weight	2.3 kg

Contractual warranty


Warranty	18 months
----------	-----------

Dimensions




(1) Position Emergency STOP

Protective Cable Sleeves




(2) Internal $\varnothing$ (mm/in.)



(2) Internal ø (mm/in.)


Mounting of Pendant Box



- 1 : Sustentation cables
- 2 : Cables clamp
- 3 : Ring


Control of Single-Speed Reversing Motor

With XESD1181 contact block, to be ordered separately



Control of 2-Speed Reversing Motor

With XESD1281 contact block, to be ordered separately



KM High speed contactor