

## Product data sheet

### Characteristics

# XAWF310EX

Control station, metal, three functions, 3 flush push buttons, green, red, black, 2 NO + 1 NC, ATEX



### Main

Range of product	Harmony XAW
Product or component type	Complete control station
Device short name	XAWF
Control station application	Three functions
Material	Metal
Control station composition	1 flush push-button, green, spring return 1 NO 1 flush push-button, red, spring return 1 NC 1 flush push-button, black, spring return 1 NO

### Complementary

Colour of base of enclosure	Black
Colour of cover	Black
Cable entry	1 entry for ISO M20 cable gland
Width	80 mm
Depth	77 mm
Height	175 mm
Net weight	1.545 kg
Marking	Ex tb IIIC T85°C Db IP65
Mechanical durability	5000000 cycles
Short-circuit protection	10 A cartridge fuse type gG
[Ie] rated operational current	3 A at 240 V, AC-15, A600 conforming to IEC 60947-5-1 6 A at 120 V, AC-15, A600 conforming to IEC 60947-5-1 0.1 A at 600 V, DC-13, Q600 conforming to IEC 60947-5-1 0.27 A at 250 V, DC-13, Q600 conforming to IEC 60947-5-1 0.55 A at 125 V, DC-13, Q600 conforming to IEC 60947-5-1 1.2 A at 600 V, AC-15, A600 conforming to IEC 60947-5-1

### Environment

Ambient air temperature for operation	-20...60 °C
Overvoltage category	I conforming to IEC 60536
IP degree of protection	IP65 conforming to IEC 60529
Standards	IEC 60079-0:2009 EN 60079-31:2009 IEC 60947-5-4 IEC 61000-6-2 IEC 60947-1 IEC 60947-5-1 IEC 60079-0:2007 IEC 60079-31:2008
Directives	94/9/EC - ATEX directive
Dust zone	Zone 21 - 22
Product certifications	INERIS 04ATEX0023X

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.500 cm
Package 1 Width	9.000 cm
Package 1 Length	23.500 cm
Package 1 Weight	1.626 kg
Unit Type of Package 2	S02
Number of Units in Package 2	4
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.884 kg

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------