


Product data sheet

Characteristics

XCRZ02

limit switch lever XCRZ - thermoplastic roller lever for limit switch



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	XCRZ
Product compatibility	XCRB XCRA
Movement of operating head	Rotary
Type of operator	Roller lever
Type of approach	Lateral approach
Positive opening	With

Complementary

Associated complete product	XCRB15 XCRB12 XCRB51 XCRA52 XCRA51 XCRB11 XCRA55 XCRA12 XCRB55 XCRA11 XCRA15 XCRB52
-----------------------------	--

Environment

Ambient air temperature for operation	-25...70 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.0 cm
Package 1 Width	1.8 cm
Package 1 Length	3.0 cm
Package 1 Weight	50.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------