

# Product data sheet

## Characteristics

# XS7C1A1PAL01M12

inductive sensor XS7 40x40x15 - PBT -  
Sn15mm - 12..24VDC - M12 0.15m



### Main

|                                    |                                                         |
|------------------------------------|---------------------------------------------------------|
| Range of product                   | Telemecanique Inductive proximity sensors XS            |
| Series name                        | General purpose                                         |
| Sensor type                        | Inductive proximity sensor                              |
| Device application                 | -                                                       |
| Sensor name                        | XS7                                                     |
| Sensor design                      | Flat form 40 x 40 x 15                                  |
| Size                               | 15 mm                                                   |
| Body type                          | Fixed                                                   |
| Detector flush mounting acceptance | Flush mountable                                         |
| Material                           | Plastic                                                 |
| Enclosure material                 | PBT                                                     |
| Type of output signal              | Discrete                                                |
| Wiring technique                   | 3-wire                                                  |
| Discrete output function           | 1 NO                                                    |
| Output circuit type                | DC                                                      |
| Discrete output type               | PNP                                                     |
| Electrical connection              | Remote male connector M12, 4 pins                       |
| Cable length                       | 0.15 m                                                  |
| [Us] rated supply voltage          | 12...24 V DC with reverse polarity protection           |
| Switching capacity in mA           | <= 100 mA DC with overload and short-circuit protection |
| IP degree of protection            | IP67 double insulation conforming to IEC 60529          |

### Complementary

|                          |                              |
|--------------------------|------------------------------|
| Detection face           | Frontal                      |
| Front material           | PBT                          |
| Operating zone           | 0...12 mm                    |
| Differential travel      | 1...15% of Sr                |
| Wire insulation material | PVC                          |
| Status LED               | Output state: 1 LED (yellow) |
| Supply voltage limits    | 10...36 V DC                 |
| Switching frequency      | <= 1000 Hz                   |
| Maximum voltage drop     | <2 V (closed)                |
| Current consumption      | <= 10 mA no-load             |
| Maximum delay first up   | 10 ms                        |
| Maximum delay response   | 2 ms                         |
| Maximum delay recovery   | 5 ms                         |
| Marking                  | CE                           |
| Depth                    | 15 mm                        |
| Height                   | 40 mm                        |
| Width                    | 40 mm                        |

## Environment

|                                       |                                                                         |
|---------------------------------------|-------------------------------------------------------------------------|
| Product certifications                | UL[RETURN]C-Tick[RETURN]Ecolab[RETURN]CSA                               |
| Ambient air temperature for operation | -25...70 °C                                                             |
| Ambient air temperature for storage   | -40...85 °C                                                             |
| Vibration resistance                  | 25 gn amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6 |
| Shock resistance                      | 50 gn for 11 ms conforming to IEC 60068-2-27                            |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 4.2 cm    |
| Package 1 Width              | 9.2 cm    |
| Package 1 Length             | 6.8 cm    |
| Package 1 Weight             | 76.0 g    |
| Unit Type of Package 2       | S02       |
| Number of Units in Package 2 | 22        |
| Package 2 Height             | 15.0 cm   |
| Package 2 Width              | 30.0 cm   |
| Package 2 Length             | 40.0 cm   |
| Package 2 Weight             | 2.213 kg  |
| Unit Type of Package 3       | P06       |
| Number of Units in Package 3 | 352       |
| Package 3 Height             | 77.0 cm   |
| Package 3 Width              | 80.0 cm   |
| Package 3 Length             | 60.0 cm   |
| Package 3 Weight             | 42.532 kg |


## Offer Sustainability

|                            |                                                                                                                       |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                 |
| REACH Regulation           |  <a href="#">REACH Declaration</a> |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)                                                            |
| Mercury free               | Yes                                                                                                                   |
| RoHS exemption information |  <a href="#">Yes</a>               |
| Circularity Profile        | No need of specific recycling operations                                                                              |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Dimensions



(1) LED

(2) For CHC type screws


---

## Setting-up

---


### Minimum Mounting Distances (mm)

Side by Side




$$e (1) \geq 45$$

Face to Face



$$e (2) \geq 110$$


Facing a Metal Object



$$e (3) \geq 45$$

## Wiring Schemes

### PNP



### M12

