

# Product data sheet

## Characteristics

# XVR1M08

## 230VAC 25W ROTATING BEACON (YELLOW)



### Main

Range of product	Harmony XVR Application
Product or component type	Rotating mirror beacon
Component name	XVR
Mounting diameter	165 mm
Light source	Bulb included, yellow
Bulb type	Incandescent with BA 15d base
Power dissipation in W	25 W
[Us] rated supply voltage	230 V AC

### Complementary

Material	Glass reinforced polyamide 6: base unit Polycarbonate: domed lens unit
Clamping connection capacity	$\leq 1 \times 1.5 \text{ mm}^2$
Cable entry	1 tapped entry for cable gland (included) for M20
[Ui] rated insulation voltage	250 V conforming to EN/IEC 60947-1
Current consumption	$< 110 \text{ mA}$
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 60947-1
Service life in hours	2000 h
Operating position	Horizontal
Flashing frequency	3 Hz
CAD overall width	165 mm
CAD overall height	202 mm
CAD overall depth	165 mm
Net weight	1.235 kg

### Environment

Standards	UL 508 EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	$-40 \dots 70 \text{ }^\circ\text{C}$
Ambient air temperature for operation	$-20 \dots 50 \text{ }^\circ\text{C}$
Electrical shock protection class	Class I conforming to EN/IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
NEMA degree of protection	NEMA 4X conforming to UL 508 (indoor) NEMA 4X conforming to CSA C22 (indoor)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------