

## Product data sheet

### Characteristics

# XZCB4L0100

PvR cable - 4 x 0.5 mm<sup>2</sup> - length 100 m



### Main

Accessory / separate part type	Cable
--------------------------------	-------

### Complementary

Accessory / separate part designation	Bare cable
Accessory / separate part category	Cabling accessories
Cable length	100 m
Material	PvR (PVC/NBR) sheath
Colour	Matt black
Cable cross section	0.5 mm <sup>2</sup>
Total number of wires	4
Wire insulation material	PVC
Flame retardance	Class C2 conforming to NF C 32-070
[Ue] rated operational voltage	300 V
[Ui] rated insulation voltage	2000 V conforming to NF C 32-201-1
Bending radius	Minimum 3 x external diameter
Tensile strength	10...35 N/mm <sup>2</sup>
Hardness	70 shores A (tolerance: +/-5)
Net weight	4.49 kg

### Environment




Ambient air temperature for operation	-35...90 °C
Ambient air temperature for storage	-40...100 °C
Environmental characteristic	Synthetic oils at 90 °C Mineral resistant at 90 °C Soluble resistant at 90 °C Without un moulding agent

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.500 cm
Package 1 Width	25.000 cm
Package 1 Length	25.000 cm
Package 1 Weight	4.587 kg
Unit Type of Package 2	S03
Number of Units in Package 2	2

Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	9.672 kg

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------