

Product data sheet

Characteristics

XZCC8FCM40S

female, M8, 4-pin, elbowed connector - cable gland M9.5 x 1



Main

| | |
|------------------------------------|--|
| Range of product | Telemecanique Cabling components |
| Accessory / separate part category | Cabling accessories |
| Accessory / separate part type | Connector |
| Electrical connection | Elbowed female connector M8, 4 pins |
| Collar material | Metal |
| Status LED | Without |
| Cable connection | Solder terminal / wire size <0.25 mm ² / clamping capacity 5 mm |

Complementary

| | |
|--------------------------------|--------------------|
| Cable gland type | M9.5 |
| Cable connector fixing | Screw-on |
| [Ue] rated operational voltage | 60 V AC 75 V DC |
| [In] rated current | 4 A |
| Enclosure material | Plastic |
| Minimum insulating resistance | 1 GΩ |
| Contact resistance | 5000 μOhm |
| Net weight | 0.01 kg |



Environment

| | |
|---------------------------------------|-------------|
| IP degree of protection | IP67 |
| Ambient air temperature for operation | -40...85 °C |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.900 cm |
| Package 1 Width | 2.400 cm |
| Package 1 Length | 7.200 cm |
| Package 1 Weight | 10.000 g |
| Unit Type of Package 2 | S01 |
| Number of Units in Package 2 | 50 |
| Package 2 Height | 15 cm |
| Package 2 Width | 15 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 642.000 g |


Offer Sustainability

| | |
|----------------------------|---|
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free | Yes |
| RoHS exemption information |  Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions



(1) Cable gland : M9.5 x 1

Connections and Schemes

