

Product data sheet

Characteristics

ZCKY53

limit switch lever ZCKY - metal round rod lever
3 mm L=125 mm - -40..120 °C



Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKJ
Associated head	ZCKE05
Movement of operating head	Rotary
Type of operator	Rod lever spring return metal (round rod 3 mm, L = 125 mm)
Type of approach	Lateral approach

Complementary

Switch actuation	By any moving part
Positive opening	Without



Environment

Ambient air temperature for operation	-25...70 °C for standard environment -40...70 °C for low temperature 10...120 °C for high temperature
Ambient air temperature for storage	-40...70 °C standard environment -40...70 °C low temperature 10...120 °C high temperature
Environmental characteristic	High temperature Low temperature Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	2.200 cm
Package 1 Length	12.500 cm
Package 1 Weight	18.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	100
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.171 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------