


Product data sheet

Characteristics

NSYSPS5100

Spacial SF/SM side panel plinth - 100x500 mm



Main

Range	Spacial
Accessory / separate part category	Enclosure accessory
Product or component type	Plinth side panel
Application	Prisma application Multi-purpose
Nominal dimensions of the housing	-
Device composition	Fixing elements 4 corner cover 2 side panel
Range compatibility	Spacial Spacial SF Spacial Spacial SM Prisma Prisma PH
Mounting support	Front plinth

Complementary

Fixing mode	By screws
Colour	Grey (RAL 7022)
Surface finish	Epoxy-polyester powder
Height	100 mm
Width	Nominal: 500 mm

Environment

IP degree of protection	IP20 (complete plinth)
IK degree of protection	IK10

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	12.000 cm
Package 1 Length	35.500 cm
Package 1 Weight	1.406 kg
Unit Type of Package 2	S03
Number of Units in Package 2	8
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	11.668 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 mois
----------	---------