



### Main

Range	Mureva
Product name	Mureva Enclosure
Product or component type	Weatherproof enclosure
Enclosure type	Mini enclosure for modular device
Mounting plate description	Slotted

### Complementary

Enclosure mounting	Surface
9 mm pitches	8
Number of 18 mm modules per row	4
Total number of 18 mm modules	4
Number of horizontal rows	1
Electrical insulation class	Class II Double insulation
Provided equipment	1 marking kit
Type of front cover	Transparent
Power dissipation in W	10 W
[In] rated current	63 A
Type of rail	DIN
Number of pre-cutouts PG ISO	3
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Width	123 mm
Height	200 mm
Depth	112 mm
Internal depth	56 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

### Environment

Standards	IEC 61439-3 IEC 60695-2-1 EN 50262 IEC 60670
Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.200 cm
Package 1 Width	20.000 cm
Package 1 Length	12.200 cm
Package 1 Weight	464.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	9
Package 2 Height	22.000 cm
Package 2 Width	35.000 cm
Package 2 Length	41.000 cm
Package 2 Weight	4.520 kg
Unit Type of Package 3	P12
Number of Units in Package 3	216
Package 3 Height	80.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	118.080 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product
Minimum percentage of recycled plastic content	25

## Contractual warranty

Warranty	18 months
----------	-----------