



Main

Range of product	ComPact NS630b...1600
Device short name	Modbus COM
Product or component type	Communication module
Range compatibility	ComPact ComPact NS630b...1600

Complementary

Communication network type	Modbus
Mounting mode	Drawout
Control type	Manually operated
Localisation on device	Behind control unit
[Us] rated supply voltage	24 V DC
Maximum supply current	0.03 A
Height	90 mm
Width	54 mm
Depth	58 mm

Environment

IP degree of protection	IP40
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	7.6 cm
Package 1 Length	9.3 cm
Package 1 Weight	1.086 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
