



### Main

Product or component type	Auxiliary contact
Device short name	PF
Range compatibility	Masterpact MasterPact NT Masterpact MasterPact NW
Signal contacts composition	1 NO/NC

### Complementary

Auxiliary contacts type	Low level
Mounting mode	Fixed
Breaking capacity (A)	DC-12: 0.15 A at 250 V DC DC-12: 3 A at 24/48 V DC AC-12: 3 A at 24/48 V AC 50/60 Hz AC-12: 3 A at 240 V AC 50/60 Hz DC-12: 0.3 A at 125 V DC AC-12: 3 A at 380 V AC 50/60 Hz

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	11.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	40.0 g

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

### Contractual warranty

Warranty	18 months
----------	-----------