




Main

Range	MasterPacT
Range of product	MasterPact NT MasterPact NW MasterPact NW DC
Device short name	second MX
Product or component type	Voltage release
Device application	Control
Voltage release type	Second opening coil Instantaneous voltage release
Control type	Standard
[Uc] control circuit voltage	200...250 V AC 50/60 Hz 200...250 V DC
Circuit breaker mounting mode	Fixed
Range compatibility	Masterpact MasterPact NT Masterpact MasterPact NW Masterpact MasterPact NW DC

Complementary

Operating threshold	0.7...1.1 x Un opening
Response time	50 ms +/- 10 % for MasterPact NT 50 ms +/- 10 % for MasterPact NW
Supply holding power	4.5 VA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	6.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	1.162 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------