



Main

Product or component type	Auxiliary contact
Device short name	SDE
Range compatibility	Masterpact MasterPact NT
Signal contacts composition	1 NO/NC

Complementary

Auxiliary contacts type	Standard
Mounting mode	Drawout
[I _{th}] conventional free air thermal current	5 A
Breaking capacity (A)	DC-12: 0.15 A at 250 V DC DC-12: 3 A at 24/48 V DC DC-12: 0.3 A at 125 V DC
Minimum load	100 mA at 24 V

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	18.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	43.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------