



Main

Range of product	MasterPact NW
Device short name	Eco Modbus COM
Product or component type	Communication module
Range compatibility	Masterpact MasterPact NW

Complementary

Communication network type	Eco Modbus
Mounting mode	Drawout
Localisation on device	Basic frame
[Us] rated supply voltage	24 V DC
Maximum supply current	0.03 A
Height	90 mm
Width	54 mm
Depth	58 mm

Environment

IP degree of protection	IP40
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	7.600 cm
Package 1 Length	9.300 cm
Package 1 Weight	1.089 kg
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	11.090 kg
Unit Type of Package 3	P12
Number of Units in Package 3	320
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	366.880 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------