

Main

| | |
|---------------------------|---------------|
| Range | Mureva |
| Product or component type | Socket |
| Device short name | Mureva socket |
| Plug, socket category | Low voltage |
| Poles description | 3P + E |
| Network type | AC |
| Outlet standard | Industrial |

Complementary

| | |
|-------------------------------------|---|
| Mounting mode | Wall-mounted |
| Plug, socket, control station shape | Angled |
| [In] rated current | 63 A |
| [Ue] rated operational voltage | 380...415 V |
| Network frequency | 50/60 Hz |
| Ground lug clockwise position | 6 h |
| Plug, socket material | Housing: self-extinguishing engineering polymer |
| Contacts material | Pins: stainless steel Sleeves: nickel plated brass Springs: stainless steel |
| Connections - terminals | Captive screws, completely loosened |
| Cable cross section | 6...25 mm ² |
| Cable entry | Cable gland |
| Thread type | Pg 36 |
| Net weight | 0.987 kg |
| Base dimension | 104 x 162 mm |
| Height | 255 mm |
| Width | 104 mm |
| Depth | 180 mm |
| Colour | Grey (RAL 7035) |
| Voltage colour | Red |

Environment

| | |
|---------------------------------------|---|
| Standards | EN 60309-2 EN 60309-1 |
| IP degree of protection | IP67 conforming to IEC 60529 |
| IK degree of protection | IK08 conforming to EN 62262 |
| Fire resistance | 850 °C conforming to IEC 60695-2-11 |
| Relative humidity | 50 % at 40 °C 70 % at 30 °C 90 % at 20 °C |
| Ambient air temperature for operation | 35 °C (86400 s) |

Packing Units

| | |
|------------------------------|------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 18.500 cm |
| Package 1 Width | 10.500 cm |
| Package 1 Length | 25.000 cm |
| Package 1 Weight | 1.003 kg |
| Unit Type of Package 2 | S03 |
| Number of Units in Package 2 | 5 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 30.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 5.530 kg |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 40 |
| Package 3 Height | 50.000 cm |
| Package 3 Width | 80.000 cm |
| Package 3 Length | 120.000 cm |
| Package 3 Weight | 55.816 kg |

Offer Sustainability

| | |
|---|---|
| Packaging without single use plastic | No |
| Packaging made with recycled cardboard | Yes |
| SCIP Number | 89350e0d-a4ac-4516-bf86-fdaed8a227fc |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| Take-back | No |
| Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) | 39 |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|