



## Main

|                           |               |
|---------------------------|---------------|
| Range                     | Mureva        |
| Product or component type | Socket        |
| Device short name         | Mureva socket |
| Plug, socket category     | Low voltage   |
| Poles description         | 3P + N + E    |
| Network type              | AC            |
| Outlet standard           | Industrial    |

## Complementary

|                                     |   |
|-------------------------------------|---|
| Mounting mode                       | Panel-mounted   |
| Plug, socket, control station shape | Angled  |
| [In] rated current                  | 63 A  |
| [Ue] rated operational voltage      | 380...415 V   |
| Network frequency                   | 50/60 Hz  |
| Ground lug clockwise position       | 6 h   |
| Plug, socket material               | Housing: self-extinguishing engineering polymer                                   |
| Contacts material                   | Pins: stainless steel<br>Sleeves: nickel plated brass<br>Springs: stainless steel |
| Connections - terminals             | Captive screws, completely loosened   |
| Cable cross section                 | 6...25 mm <sup>2</sup>  |
| Net weight                          | 0.52 kg   |
| Base dimension                      | 100 x 107 mm  |
| Height                              | 107 mm  |
| Width                               | 100 mm  |
| Depth                               | 129 mm  |
| Colour                              | Grey (RAL 7035)   |
| Voltage colour                      | Red   |

## Environment

|                                       |   |
|---------------------------------------|---|
| Standards                             | EN 60309-1<br>EN 60309-2                        |
| IP degree of protection               | IP67 conforming to IEC 60529                    |
| IK degree of protection               | IK08 conforming to EN 62262                     |
| Fire resistance                       | 850 °C conforming to IEC 60695-2-11             |
| Relative humidity                     | 50 % at 40 °C<br>70 % at 30 °C<br>90 % at 20 °C |
| Ambient air temperature for operation | 35 °C ( 86400 s )                               |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 11.8 cm  |
| Package 1 Width              | 12.0 cm  |
| Package 1 Length             | 12.9 cm  |
| Package 1 Weight             | 530.0 g  |
| Unit Type of Package 2       | S03      |
| Number of Units in Package 2 | 15       |
| Package 2 Height             | 30.0 cm  |
| Package 2 Width              | 30.0 cm  |
| Package 2 Length             | 40.0 cm  |
| Package 2 Weight             | 8.437 kg |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product                                      |
| REACH Regulation           | <a href="#">REACH Declaration</a>                          |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free               | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                     |
| RoHS exemption information | <a href="#">Yes</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>              |
| Circularity Profile        | No need of specific recycling operations                   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|