

### Main

Range	Mureva
Product or component type	Interlocked socket
Device short name	Mureva socket
Plug, socket category	Low voltage
Poles description	3P + E
Network type	AC
Outlet standard	Industrial

### Complementary

[In] rated current	125 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Protection type	Residual current breaker with overcurrent protection (RCBO)
Plug, socket material	Housing: self-extinguishing engineering polymer
Connections - terminals	Captive screws
Cable cross section	16...95 mm <sup>2</sup>
Cable entry	Cable gland
Thread type	Pg 42
Net weight	11.1 kg
Height	710 mm
Width	270 mm
Depth	215 mm
Colour	Grey (RAL 7035)
Voltage colour	Red

### Environment

Standards	EN 60309-2 EN 60309-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	960 °C conforming to IEC 60695-2-11
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient air temperature for operation	35 °C ( 86400 s )

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	29.0 cm
Package 1 Width	27.0 cm
Package 1 Length	70.0 cm
Package 1 Weight	11.1 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------