

Main

Range	PratiKa
Product or component type	Socket
Device short name	PratiKa socket
Plug, socket category	Low voltage
Poles description	3P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Wall-mounted
Plug, socket, control station shape	Angled
[In] rated current	16 A
[Ue] rated operational voltage	100...130 V
Network frequency	50/60 Hz
Ground lug clockwise position	4 h
Plug, socket material	Housing: self-extinguishing engineering polymer
Contacts material	Pins: stainless steel Sleeves: nickel plated brass Springs: stainless steel
Connections - terminals	Captive screws, completely loosened
Cable cross section	1...4 mm ²
Cable outer diameter	8...15 mm
Cable entry	Cable gland
Thread type	Pg 16
Net weight	0.338 kg
Base dimension	80 x 100 mm
Height	156 mm
Width	80 mm
Depth	127 mm
Colour	Grey (RAL 7035)
Voltage colour	Yellow

Environment

Standards	EN 60309-2 EN 60309-1
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-11
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient air temperature for operation	35 °C (86400 s)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	12.7 cm
Package 1 Length	15.6 cm
Package 1 Weight	289.0 g

Offer Sustainability

SCIP Number	78fb8795-a40d-47b1-874c-18ea0cf17d72
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------