



Main

Range	PratiKa
Product or component type	Plug
Device short name	PratiKa plug
Plug, socket category	Low voltage
Poles description	2P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Wall-mounted
Plug, socket, control station shape	Angled
[In] rated current	32 A
[Ue] rated operational voltage	200...250 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Self-extinguishing engineering polymer
Contacts material	Pins: nickel plated brass
Connections - terminals	Captive screws
Cable cross section	2.5...10 mm ²
Cable outer diameter	11.5...21 mm
Net weight	0.43 kg
Base dimension	106 x 130 mm
Height	130 mm
Width	106 mm
Depth	130 mm
Colour	Grey (RAL 7035)
Voltage colour	Blue

Environment

Standards	EN 60309-1 EN 60309-2
IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-1
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Operating altitude	2000 m
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.7 cm
Package 1 Width	12.9 cm
Package 1 Length	17.7 cm
Package 1 Weight	364.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Height	12.6 cm
Package 2 Width	21.6 cm
Package 2 Length	27.0 cm
Package 2 Weight	854.0 g
Unit Type of Package 3	S03
Number of Units in Package 3	6
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	3.049 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------