



Main

| | |
|---------------------------------|----------------|
| Range of product | Harmony 9001SK |
| Product or component type | Push-button |
| Device short name | 9001SK |
| Type of operator | Spring return |
| Operator profile | Black flush |
| Operator additional information | Plastic guard |

Complementary

| | |
|-------------------------------|------------------|
| Bezel material | Plastic |
| Mounting diameter | 30 mm |
| Contacts type and composition | 1 NC |
| Contact operation | Standard |
| Mechanical durability | 5000000 cycles |
| Device presentation | Complete product |
| Cap/operator or lens colour | Black |
| Operator profile | Flush |
| Type of operator | Spring return |
| Size | 30 mm |






Environment

| | |
|---------------------------|--|
| Standards | EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 852 EN/IEC 60947-1 UL 508 JIS C 4520 CSA C22.2 No 14 |
| IP degree of protection | IP66 |
| NEMA degree of protection | NEMA 1/2/3/3R/4/4X/6/12/13 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.588 cm |
| Package 1 Width | 9.652 cm |
| Package 1 Length | 4.572 cm |
| Package 1 Weight | 68.039 g |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|