



## Main

Range of product	Mureva
Product or component type	Junction box
Colour tint	Grey (RAL 7035)

## Complementary

Device mounting	Surface
Fixing mode	By screws: cover
Base dimension	225 x 175 x 100 mm
Material	PP (polypropylene): body and cover
Height	242 mm
Width	292 mm
Depth	128 mm

## Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP55
IK degree of protection	IK07
Glow wire temp	750 °C
Standards	EN 60670 CE

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	24.5 cm
Package 1 Length	29.5 cm
Package 1 Weight	860 g
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	40 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	8.18 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	200
Package 3 Height	220 cm
Package 3 Width	100 cm

Package 3 Length	120 cm
Package 3 Weight	223 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations