



## Main

Range	Unica
Product type	Floor outlet box
Device application	Power socket distribution
Cabling installation system	Floor outlet box
Type of floor	Raised floor In-cavity floor Hollow core floor
Floor box shape	Rectangular
Colour	Grey

## Complementary

Device presentation	Complete product
Product compatibility	Unica outlet - 45 mm x 45 mm Unica outlet - 45 mm x 90 mm
Size	Housing: M
Device mounting	Floor mounted
Fixing mode	Snap-fitted Strain relief
Product material	Metal brushed finish
Height	82 mm
Width	200 mm
Depth	200 mm

## Environment

IK degree of protection	IK09
IP degree of protection	IP24
Market segment	Commercial Office School

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	21.0 cm
Package 1 Length	23.5 cm
Package 1 Weight	2.244 kg
Unit Type of Package 2	S03
Number of Units in Package 2	4
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.417 kg
Unit Type of Package 3	P12
Number of Units in Package 3	96

Package 3 Height	110.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	238.008 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations