



Main

Range	Linergy
Range of product	Linergy
Product or component type	Bar
Product name	Linergy TB
Accessory / separate part category	Earthing accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure PrismaSeT PrismaSeT P cubicle
Provided equipment	40 clamps 1 35 mm² terminal

Complementary

Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm Pack enclosure - width 550 mm
Quantity per set	Set of 1
Length	450 mm
Width	13 mm
Depth	12 mm
Net weight	0.36 kg
Colour	Natural

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.300 cm
Package 1 Width	3.300 cm
Package 1 Length	51.000 cm
Package 1 Weight	348.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	30
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	11.306 kg
Unit Type of Package 3	P12
Number of Units in Package 3	360
Package 3 Height	103.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	145.000 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product