



Main

| | |
|---------------------|--|
| Range | Thalassa |
| Product name | Thalassa PLS |
| Device short name | PLS |
| Enclosure type | Multi-purpose |
| Category | Insulating modular box |
| Nominal height | 540 mm |
| Nominal width | 720 mm |
| Nominal depth | 230 mm |
| Enclosure mounting | Wall mounted |
| Device composition | 1 cover: on enclosure 1 rear part: on enclosure Locking screws |
| Supply | Set of 14 |
| Body type | One piece moulded |
| Type of front cover | High transparent cover |
| Lock type | Slot screw |

Complementary

| | |
|------------------------|--|
| Removable parts | Cover locking screw |
| Material | Cover: polycarbonate Rear: polyester reinforced with fibreglass |
| Colour | Body: grey (RAL 7032) |
| Standards | NEMA 4X NEMA classification 13 IEC 62208 |
| Product certifications | UL |

Environment

| | |
|-------------------------------------|--------------------------------|
| Electrical insulation class | Class II |
| IP degree of protection | IP65 conforming to IEC 60529 |
| IK degree of protection | IK09 conforming to IEC 62262 |
| Fire resistance | 960 °C conforming to IEC 62208 |
| Ambient air temperature for storage | -30...120 °C |