



Main

Range	Exiway
Product name	Exiway One
Product or component type	Emergency luminaire
Device application	Anti-panic lighting
Function	Self-test
Operational mode	Maintained
Number of batteries	1 x 6 V 1.5 Ah Ni-Cd (Nickel-Cadmium)
Light source	Fluorescent tube G5 8 W
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

Mounting support	Ceiling False ceiling Wall
[Ue] rated operational voltage	230 V 50 Hz
Power consumption in VA	18.6 VA
Power consumption in W	7.2 W
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Type of glass	Fresnel glass
Height	160 mm
Depth	68 mm
Width	375 mm






Environment

IP degree of protection	IP65
IK degree of protection	IK07
Fire resistance	850 °C
Product certifications	ENEC
Ambient air temperature for operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	16.4 cm
Package 1 Length	38.1 cm
Package 1 Weight	1.22 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------