



## Main

Range	Exiway
Product name	Exiway One
Product or component type	Emergency luminaire
Device application	Anti-panic lighting
Function	Standard
Operational mode	Non-maintained
Number of batteries	1 x 4.8 V 4 Ah Ni-Cd (Nickel-Cadmium)
Colour tint	White
Light source	Fluorescent tube 2G7 11 W
Light source colour	White
Cover type	Transparent
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

## Complementary

Mounting support	Ceiling False ceiling Wall
[Ue] rated operational voltage	220...230 V AC/DC 50 Hz
Power consumption in VA	8.4 VA
Power consumption in W	1.6 W
Current consumption	36 mA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 h
Type of glass	Fresnel glass
Material	Housing: plastic Cover: plastic
Height	146 mm
Depth	62 mm
Width	300 mm






## Environment

IP degree of protection	IP65
IK degree of protection	IK07
Fire resistance	850 °C
Product certifications	AENOR[RETURN]ENEC
Ambient air temperature for operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------