



Main

Range	Pragma
Product or component type	Door
Accessory / separate part category	Enclosure accessories

Complementary

Enclosure mounting	Flush Surface
Key number	Number to be stated
Type of front cover	Transparent
Door opening side	Right or left
Number of horizontal rows	1
9 mm pitches	36
Number of 18 mm modules per row	18
Total number of 18 mm modules	18
Installation description	Surface mounting Flush mounting
Enclosure material	Technoplastic
Width	426 mm
Height	300 mm
Depth	20 mm
Colour	Smoked

Environment






Fire resistance	750 °C
IP degree of protection	IP40
IK degree of protection	IK09
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	50.0 cm
Package 1 Length	37.0 cm
Package 1 Weight	800.0 g
Unit Type of Package 2	P12
Number of Units in Package 2	98
Package 2 Height	119.0 cm

Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	78.4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------