



Overview

Presentation	Nicht zur Verwendung durch Verbraucher bestimmt. Leistungsstarker Stromschutz für Server und Netzwerke
Lead time	Usually in Stock

Main

Product or component type	Battery accessory
Number of rack unit	4U
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	Rack mounting brackets User manual

Batteries & Runtime

Number of battery free slots	2
Number of battery filled slots	2
Device mounting	19 inch battery tray
Number of battery replacement quantity	2

Physical

Colour	Black
Height	17.8 cm
Width	48.3 cm
Depth	64 cm
Net weight	65.46 kg
Mounting mode	Not rack-mountable

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-55...60 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	34.3 cm
Package 1 Width	81.3 cm
Package 1 Length	58.4 cm
Package 1 Weight	75 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Lead free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Take-back	Take-back program available

Contractual warranty

Warranty	2 Jahre Garantie für Reparatur/Ersatz, optional on-site warranties available, Optional erweiterte Garantien verfügbar
----------	---