



Ana

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VCF
Product Type	Acil durdurma yük ayırıcısı

Tamamlayıcı

Device Composition	Anahtar Kol
Mounting Support	Kol: kapı Anahtar: kapı
Mounting Method	4 vidayla için kol
Performance Level	Yüksek performans
Number of Poles	3P
Contact Type and Composition	3 NA
[Ue] IEC Rated Operational Voltage	690 V AC 50/60 Hz
IEC Rated Operational Power in W	11 KW -de 500 V (AC-23A) 11 KW -de 690 V (AC-3) 15 KW -de 690 V (AC-23A) 4 KW -de 230...240 V (AC-3) 5,5 KW -de 400...415 V (AC-3) 7,5 KW -de 500 V (AC-3) 5,5 KW -de 230...240 V (AC-23A) 7,5 kW -de 400...415 V (AC-23A)
[Ie] Rated Operational Current	14,5 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	25 A
[Ithe] Conventional Enclosed Thermal Current	20 A
Making Capacity (I Rms)	250 A -de 400 V AC-21A 250 A -de 400 V AC-22A 250 A -de 400 V AC-23A
Breaking Capacity	200 A -de 400 V (AC-21A) 200 A -de 400 V (AC-22A) 200 A -de 400 V (AC-23A)
Rated Conditional Short Circuit Current	10 KA -de 400 V - ilgili sigorta 25 A AM 10 kA -de 400 V - ilgili sigorta 25 A GG
[Icm] Rated Short Circuit Making Capacity	1 kA -de 400 V ltepe'de
[Icw] Rated Short Time Withstand Current	300 A -de 400 V 1 s
[Uimp] Rated Impulse Withstand Voltage	8 kV
Suitability for Isolation	Evet
Network Type	AC DC
Intermittent Duty Class	30
Control Type	Döner kol
Rotary Handle Mounting Style	Doğrudan
Handle Color	Kırmızı

Handle Front Plate Color	Sarı
Rotary Handle Padlocking	1 ila 3 asmalı kilit 4...8 mm
Marking	0 - 1
Mechanical Durability	100000 cycles
Electrical Durability	100000 Cycles AC-21 30000 cycles DC-1...5
IEC Terminal Connection	Güç devresi: vida kelepçesi terminalleri kablo 10 mm ² - kablo sertliği: katı Güç devresi: vida kelepçesi terminalleri kablo 6 mm ² - kablo sertliği: esnek - Kablo uçlu
Tightening Torque	Güç devresi: 2,1 N.m - üzerinde vida kelepçesi terminalleri
Base Dimension	60 x 60 mm
Height	74 mm
Width	60 mm
Product Weight	0,25 kg

Ortam

Standards	IEC 60947-3
Product Certifications	CSA[RETURN]CCC[RETURN]GL[RETURN]UL[RETURN]UKCA
Degree of Protection	IP20 'e uygunIEC 60529 IP65
Protective Treatment	TC
Mechanical Robustness	Titreşimler 10...150 Hz (1 gn) 'e uygunIEC 60068-2-6 Şoklar 11 ms (30 Gn) 'e uygunIEC 60068-2-27
Ambient Air Temperature for Operation	-20...50 °C
Fire Resistance	960 °C 'e uygunIEC 60695-2-1
Compatibility Code	Ana yük ayırıcı

Paketleme üniteleri

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8,000 cm
Package 1 Width	8,500 cm
Package 1 Length	12,000 cm
Package 1 Weight	219,000 g
Unit Type of Package 2	S03
Number of Units in Package 2	24
Package 2 Height	30,000 cm
Package 2 Width	30,000 cm
Package 2 Length	40,000 cm
Package 2 Weight	5,669 kg
Unit Type of Package 3	P06
Number of Units in Package 3	192
Package 3 Height	75,000 cm
Package 3 Width	80,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	53,352 kg

Sürdürülebilirlik Teklifi

Sürdürülebilirlik teklif durumu	Green Premium ürünü
REACH Düzenlemesi	 REACH Bildirisi
EU RoHS Direktifi	Muafiyetlerle uyumlu
Toksik ağır metal içermez	Evet
Cıva içermez	Evet
Çin RoHS Düzenlemesi	 Çin RoHS Beyanı
RoHS muafiyet bilgileri	 Evet

Çevre Beyanı	 Çevresel Ürün Profili
Döngüsellik Profili	Belirli geri dönüşüm işlemlerine gerek yoktur
WEEE	Ürün, Avrupa Birliği pazarlarında özel atık toplama ilkelerine uygun şekilde atılmalıdır ve hiçbir suretle çöp kutularına bırakılmamalıdır.
PVC içermez	Evet
Halojen içerik performansı	Halojen içermeyen ürün

Sözleşme garantisi

Garanti	18 months
---------	-----------