

Product data sheet

Characteristics

XS7T2NC440

Induktivni senzor XS7 26x26x26 – plastika – Sn
10 mm – 12 do 48 V DC – kabel 2 m



Glavno

Serijska izdelka	Telemecanique Inductive proximity sensors XS
Ime serije	Glavni namen
Tip senzorja	Induktivni senzor bližine
Uporaba izdelka za specifične aplikacije	-
Ime senzorja	XS7
Zasnova senzorja	Kubična oblika 26 x 26 x 26
Velikost	26 mm
Tip ohišja	Fiksen
Detector flush mounting acceptance	Podometno montirano
Material	Plastika
Material omare	Plastika
Tip izhodnega signala	Diskretni
Tehnika ožičenja	4-žični
[Sn] Nazivna razdalja zaznavanja	10 Mm
Diskretni izhod funkcija	1 NO + 1 NC
Tip izhodnega tokokroga	DC
Diskretni izhod tip	NPN
Električna povezava	Kabel
Dolžina kabla	2 M
[Us] Nazivna napajalna napetost	12 do 48 V DC
Preklopna zmogljivost v mA	<= 200 mA
IP stopnja zaščite	IP67

Komplementarno

Detection face	5 položajev stolpne glave
Prednji material	Plastika
Sestava kablov	4 x 0,34 mm ²
Izolacijski material žiče	PVC
Preklopna frekvenca	<= 1000 Hz
Oznaka	CE
Globina	26 Mm
Višina	26 Mm
Širina	26 Mm

Okolje

Certifikati izdelkov	CSA[RETURN]CCC[RETURN]UL
Temperatura okoliškega zraka za delovanje	-25...70 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Embalažna enota

Embalažna enota Paketa 1	PCE
Število enot v Paketu 1	1

Pogodbena garancija

Garancija	18 mesecev
-----------	------------