

Tehničke karakteristike proizvoda Karakteristike

ISM20104

OptiLine 45 - stub - montiranje pritezanjem -
jednostrani - anod.- 3500-3900 mm



Osnovne informacije

Range	OptiLine
Ime proizvoda	OptiLine 45
Oblik	Ovalni
Kablovski instalacioni sistem	Stub
Product type	Stub
Prezentacija uređaja	Prazno
Tip stuba	Jednostrano
Završna obrada stuba/ stubića	Anodička oksidacija
Način montaže stuba	Napregnut
Podešavanje	Podešavanje po visini: 400 mm

Dopunske informacije

Additional information	Podesivost plafonskih nosača 400 mm
Colour	Prirodna
Veličina otvora sa prednje strane	45 mm
Materijal	Aluminijum anodička oksidacija
Quantity package 1 / unit	Set od 1
Visina	3500...3900 mm
Dubina	89 mm
Širina	68 mm
Tip poklopca	1 zatvoreni poklopac cover 45 mm in aluminijum anodička oksidacija
Useful cross section	442 mm ²
Podela odeljaka	1 odeljak

Okruženje

Standardi	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 60598-2-2 IEC 1084-2-4 NF C 68-102 SS 424 10 32
Operating temperature	-25...60 °C
Ip stepen zaštite	IP30

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12,500 cm
Package 1 Width	16,000 cm
Package 1 Length	353,000 cm
Package 1 Weight	11,000 kg
Unit Type of Package 2	PAL

Number of Units in Package 2	28
Package 2 Height	70,000 cm
Package 2 Width	120,000 cm
Package 2 Length	360,000 cm
Package 2 Weight	330,000 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACh	 REACh Deklaracija
REACh bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja

Ugovorna garancija

Garancija	18 meseci
-----------	-----------