

Tehničke karakteristike proizvoda Karakteristike

METSECT5CYL1 cilindar Ø 8.5 mm - za strujni transformator TI



Osnovne informacije

Grupa proizvoda	PowerLogic
Ime proizvoda	CT
Kratko ime uređaja	cilindar
Tip proizvoda ili komponente	Cilindar
Pribor / posebna kategorija	Pribor za povezivanje
Prečnik	21,2 mm spoljašnji:

Dopunske informacije

Širina	32 mm
Iso navoj	M8
Spoljašnji prečnik kabla	21 mm
Otvor za sabirnice	32.5 x 10.5 25.5 x 15.5
Materijal	Aluminijum
Kompatibilnost	Cilindar

Okruženje

Sertifikacija proizvoda	CE[RETURN]EAC
-------------------------	---------------

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0,9 cm
Package 1 Width	10,0 cm
Package 1 Length	8,0 cm
Package 1 Weight	52,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	10,0 cm
Package 2 Width	11,0 cm
Package 2 Length	11,4 cm
Package 2 Weight	583,0 g
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	6,996 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.