

Tehničke karakteristike proizvoda Karakteristike

NU044218 Ram dekorativni 1 element IP44 beli



Osnovne informacije

Grupa proizvoda	New Unica
Primena uređaja	Montaža
Tip proizvoda ili komponente	Dekoratívni ram
Ime dekorativnog elementa	Unica System+
Broj dvostrukih modula	Jednostruki
Pravac instalacije	Horizontalno
Tip prekidača	Pojedinačno
Broj modula	2 modula
Način pričvršćivanja	Zavrtnjima
Nijansa boje	Bela (RAL 9003)

Dopunske informacije

Zaštitna oprema	Montažni ram
Materijal	Termoplastika ABS-UV stabilizovana: dekorativni ram
Završna obrada	Sjajno
Standardi	IEC 60884-1 IEC 60669-1
Širina	80 mm
Visina	90 mm
Dubina	30 mm
Masa proizvoda	0,052 kg
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Ik stepen zaštite	IK04
Ip stepen zaštite	IP44

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3,0 cm
Package 1 Width	8,0 cm
Package 1 Length	9,0 cm
Package 1 Weight	53,0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5

Package 2 Height	12,5 cm
Package 2 Width	12,5 cm
Package 2 Length	18,5 cm
Package 2 Weight	333,0 g
Unit Type of Package 3	S04
Number of Units in Package 3	90
Package 3 Height	30,0 cm
Package 3 Width	40,0 cm
Package 3 Length	60,0 cm
Package 3 Weight	6,788 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Proaktivna usaglašenost (proizvod nije u zakonskom okviru direktive EU RoHS)  EU RoHS deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja