


Tehničke karakteristike proizvoda Karakteristike

NU310318

Naizmenični prekidač 10A 1 modul beli



Osnovne informacije

Range of product	New Unica
Tip proizvoda ili komponente	Prekidač
Prezentacija uređaja	Mehanizam sa centralnom pločom
Vrsta tehnologije	Elektromehanička
Funkcija prekidača	Jednopolni naizmenični
Broj prekidača	1
Primena uređaja	Kontrola svetlosti
Nijansa boje	Bela (RAL 9003)
Tip pakovanja	Pakovanje u kesicama

Dopunske informacije

Nazivna struja	10 AX
[ue] nazivni napon	250 V
Tip mreže	AC
Mrežna frekvencija	50/60 Hz
Električna trajnost	20000 ciklusa, cos phi = 0,6
Otpornost izolacije	> 5 MOhm pri 500 V
Dielektrična snaga	2000 V
Minimalna moć isključenja opterećenja	200 operacija 1.25 In i 1.1 Un, cos phi = 0,3
Udaljenost otvaranja	> 3 mm
Izvršni organ	Preklopni prekidač
Broj modula	1 modul
Povezivanje - priključci	Priključci bez zavrtneja
Poprečni presek kabl	0...2,5 Mm ² kruti kabl 0...2,5 mm ² fleksibilni kabl
Materijal	Termoplastika ABS-UV stabilizovana: mechanism rocker PC (polikarbonat) GF10 FR: kućište CuZn37: priključci PBT (polibutilen-tereftalat) GF30: release button
Označavanje	Bez oznake
Završna obrada	Sjajno
Specific treatment - integrated within the material	Neobrađeno
Način pričvršćivanja	Utično
Širina	22,5 mm
Visina	45 mm
Dubina	34,25 mm
Dubina za ugradnju	21,15 mm
Masa proizvoda	0,0163 kg
Temperatura okoline za rad uređaja	-5...40 °C
Temperatura okoline za skladištenje	-5...50 °C
Standardi	EN 60669-1 LV direktiva EMC direktiva

Sertifikacija proizvoda	Aenor[RETURN]NF[RETURN]VDE[RETURN]EAC[RETURN]CE
Otpornost na hemijske supstance	Otporan na alkohol (70%) Otporan na alkohol (96%) Otporan na A-mlečnu kiselinu Otporan na razblaženi kvarterni amonijum Otporan na razblaženo izbeljivač Otporan na razblažen amonijak Otporan na vodu sa sapunom Otporan na čistač kristala Otporan na vodonik peroksid 10 zapremina Otporan na heksan

Okruženje

Ip stepen zaštite	IP4X
Ik stepen zaštite	IK04
Karakteristike životne sredine	Ulje UV otpornost Aceton Tečni sapun Tečnost za čišćenje prozora Benzin Alkohol Izbeljivač

Pakovanje

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2,200 cm
Package 1 Width	3,500 cm
Package 1 Length	4,500 cm
Package 1 Weight	19,000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	8,500 cm
Package 2 Width	18,500 cm
Package 2 Length	18,500 cm
Package 2 Weight	442,000 g
Unit Type of Package 3	S04
Number of Units in Package 3	400
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	9,598 kg

Održivost ponude

Status održive ponude	Green Premium proizvod
Propis REACH	 REACH Deklaracija
REACH bez SVHC	Da
EU RoHS direktiva	Usaglašeno  EU RoHS Deklaracija
Bez toksičnih teških metala	Da
Bez žive	Da
Sustainable packaging	Yes
RoHS regulativa za Kinu	 RoHS Deklaracija Za Kinu
Informacije o RoHS izuzecima	 Da
Izjava o zaštiti okoliša	 Profil Ekološke Prihvatljivosti Proizvoda
Profil cirkularnosti	Nema potrebe za namenskim operacijama recikliranja
WEEE	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.