



### Main

Range of product	9007
Series name	Heavy duty
Device short name	C
Head type	Turret head rotary lever
Type of operator	Spring return lever arm (standard pre-travel) (to be ordered separately) Drive shaft (reduced diameter to 0.306 in) lever arm
Switch actuation	CW
Cable entry	NPT conduit entry, cable outer diameter: 12.70 mm
Contacts type and composition	2 NO/2 NC
Contact operation	Snap action

### Complementary

Body material	Zinc alloy
Switch function	SPDT-DB
Contact form	Form ZZ
Contacts material	Silver alloy (Ag/Ni)
Minimum torque for tripping	0.45 N.m
Tripping angle	4 °
Maximum displacement angle	90 °
[Ie] rated operational current	10 A, A600 10 A, Q600
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	600 V
Local signalling	Without pilot light
Product certifications	CSA[RETURN]CE[RETURN]UL listed
Provided equipment	Receptacle



### Environment

Ambient air temperature for operation	-29...85 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.62 cm
Package 1 Width	11.43 cm
Package 1 Length	4.572 cm
Package 1 Weight	566.991 g

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations