



Main

Range of product	Modicon X80
Product or component type	Encoder interface module
Function available	Offset Compare Modulo Reduction Capture
Number of channels	3 SSI channel
Number of outputs	1 24 V DC reflex digital output for each SSI channel
Number of inputs	2 24 V DC capture digital inputs for the 3 SSI channels

Complementary

Data format	8...31 bits
Transmission rate	500 kbauds 200 kbauds 1 Mbauds 100 kbauds
Refresh time	1 ms
Input compatibility	24 V DC SSI absolute encoder (voltage limits: 19.2...30 V) for 200 mA per channel
Dielectric strength	1400 V DC 60 s
[Us] rated supply voltage	19.2...30 V DC, <30 mA 24 V DC, <30 mA (typical)
Protection type	Overvoltage protection DC
Current consumption	150 mA at 3.3 V DC for back plane, (typical) 250 mA at 3.3 V DC for back plane, (maximum)
Net weight	0.138 kg

Environment

Ambient air temperature for operation	0...60 °C
Operating altitude	0...4000 m
IP degree of protection	IP20
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Product certifications	CE[RETURN]RCM[RETURN]CSA[RETURN]EAC[RETURN]Merchant Navy[RETURN]UL
Standards	EN/IEC 61010-2-201 EN/IEC 61131-2 UL 61010-2-201 CSA C22.2 No 61010-2-201

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	11.000 cm
Package 1 Length	11.500 cm
Package 1 Weight	167.000 g
Unit Type of Package 2	S02

Number of Units in Package 2	15
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.800 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------